

# HIGH SPEED STEELS

App	lication	Segm	ents
-----	----------	------	------

Cutting Tools

#### **Available Product Variants**

Long Products

# **Product Description**

High-speed steel manufactured in a powder metallurgy process, with good hot hardness, compressive strength, and wear resistance. PM technology gives it good toughness and excellent workability, including the best machinability.

## **Process Melting**

Powder metallurgy

## **Properties**

- > Toughness & Ductility: high
- > Wear Resistance: good
- > Compressive strength: good
- > Edge Stability : good
- > Grindability: high
- > Hot Hardness (red hardness): good

#### **Applications**

> Gear Cutting, Shaving and Shaping Tools

# Chemical composition (wt. %)

С	S	Cr	Мо	V	W
1.3	+	4.2	5	3	6.3





## **Material characteristics**


	Compressive strength	Grindability	Red hardness	Toughness	Wear resistance	Edge Stability
BÖHLER \$792 MICROCLEAN	***	***	**	***	**	***
BÖHLER \$290 MICROCLEAN	****	*	***	**	****	****
BÖHLER \$390 MICROCLEAN	***	***	****	***	***	****
BÖHLER \$393 MICROCLEAN	***	***	****	***	***	****
BÖHLER S590 MICROCLEAN	***	***	****	***	***	***
BÖHLER S690 MICROCLEAN	***	***	**	****	***	**
BÖHLER \$790 MICROCLEAN	***	***	**	***	**	***
BÖHLER \$793 MICROCLEAN	***	***	****	***	***	***

## **Heat treatment**

Annealing					
Temperature	870 to 900 °C	870 to 900°C (1598 to 1652°F)    The steel needs to be protected against decarburization. Through heating of the material is followed by controlled, slow furnace cooling at a maxin cooling rate of 10°C (50°F) per hour, down to approx. 700°C (1292°F).    Final cooling in air.			
Stress relieving					
Temperature	600 to 650 °C Slow cooling furnace.    To relieve stresses set up by extensive machining or in tools of shape.    After through heating, hold in neutral atmosphere for 1 to 2 hours.				
Hardening and To	empering				
Temperature	1,050 to 1,180 °C	Salt bath, vacuum    Preheating: 1st stage ~ 500 °C, 2nd stage ~ 850 °C, 3rd stage ~1050 °C (for higher austenitising temperature)    Austenitising: for cutting applications at higher austenitising temperatures (>1130 °C), holding time after complete heating 80 seconds, maximum 150 seconds, to avoid material damage due to overtime.    Austenitising: for cold work applications at lower austenitising temperatures (<1100°C). Holding time after complete heating 15 to 30 min    Quenching: oil, warm bath (500 - 550 °C), gas.			
Temperature	550 to 580 °C	Slow heating to tempering temperature immediately after austenitising.    Dwell time in the furnace 1 hour per 20 mm material thickness (at least 1 hour)    Slow cooling to room temperature between each tempering step    3 tempering cycles recommended			



#### **Tempering Chart**



Holding time 3 x 2 hours Specimen size: square 25 mm

# **Physical Properties**

Temperature (°C)	20
Density (kg/dm³)	8
Thermal conductivity (W/(m.K))	24
Specific heat (kJ/kg K)	0.42
Spec. electrical resistance (Ohm.mm²/m)	0.54
Modulus of elasticity (10 <sup>3</sup> N/mm <sup>2</sup> )	230

# Thermal Expansions between 20°C | 68°F and ...

Temperature (°C)	100	200	300	400	500	600	700
Thermal expansion (10 <sup>-6</sup> m/(m.K))		11.7	12.2	12.4	12.7	13	12.9

If other available product variants are listed in addition to long products, please note that these may differ in terms of melting process, technical data, delivery and surface condition as well as available product dimensions. For mandatory technical specifications, other requirements and dimensions, please contact our regional voestalpine BÖHLER sales companies. The data contained in this brochure is merely for general information and therefore shall not be binding on the company. We may be bound only through a contract explicitly stipulating such data as binding. Measurement data are laboratory values and can deviate from practical analyses. The manufacture of our products does not involve the use of substances detrimental to health or to the ozone layer.

#### voestalpine BÖHLER Edelstahl GmbH & Co KG

Mariazeller Straße 25 8605 Kapfenberg, AT T. +43/50304/20-0 E. info@bohler-edelstahl.at https://www.voestalpine.com/bohler-edelstahl/de/

